

PROVA 710 Mikro-Ommetar (10A)

Električne specifikacije: (23°C±5°C)

(1) Manualni opsezi:

	Opseg	Rezolucija	Preciznost
10 A	400 $\mu\Omega$ ~ 4000 $\mu\Omega$	1 $\mu\Omega$	$\pm 0.25\% \pm 25 \mu\Omega$
	1.500 m Ω ~ 16.000 m Ω	1 $\mu\Omega$	$\pm 0.25\% \pm 25 \mu\Omega$
	5.000 m Ω ~ 60.000 m Ω	1 $\mu\Omega$	$\pm 0.25\% \pm 25 \mu\Omega$
1 A	4.00 m Ω ~ 40.00 m Ω	10 $\mu\Omega$	$\pm 0.25\% \pm 250 \mu\Omega$
	15.00 m Ω ~ 160.00 m Ω	10 $\mu\Omega$	$\pm 0.25\% \pm 250 \mu\Omega$
	50.00 m Ω ~ 600.00 m Ω	10 $\mu\Omega$	$\pm 0.25\% \pm 250 \mu\Omega$
100 mA	0.0400 Ω ~ 0.4000 Ω	100 $\mu\Omega$	$\pm 0.25\% \pm 2.5 \text{ m}\Omega$
	0.1500 Ω ~ 1.6000 Ω	100 $\mu\Omega$	$\pm 0.25\% \pm 2.5 \text{ m}\Omega$
	0.5000 Ω ~ 6.0000 Ω	100 $\mu\Omega$	$\pm 0.25\% \pm 2.5 \text{ m}\Omega$
10 mA	0.400 Ω ~ 4.000 Ω	1 m Ω	$\pm 0.25\% \pm 25 \text{ m}\Omega$
	1.500 Ω ~ 16.000 Ω	1 m Ω	$\pm 0.25\% \pm 25 \text{ m}\Omega$
	5.000 Ω ~ 60.000 Ω	1 m Ω	$\pm 0.25\% \pm 25 \text{ m}\Omega$
1 mA	4.00 Ω ~ 40.00 Ω	10 m Ω	$\pm 0.25\% \pm 250 \text{ m}\Omega$
	15.00 Ω ~ 160.00 Ω	10 m Ω	$\pm 0.25\% \pm 250 \text{ m}\Omega$
	50.00 Ω ~ 600.00 Ω	10 m Ω	$\pm 0.25\% \pm 250 \text{ m}\Omega$
100 μA	0.0400 k Ω ~ 0.4000 k Ω	100 m Ω	$\pm 0.75\% \pm 3 \Omega$
	0.1500 k Ω ~ 1.6000 k Ω	100 m Ω	$\pm 0.75\% \pm 3 \Omega$
	0.5000 k Ω ~ 6.0000 k Ω	100 m Ω	$\pm 0.75\% \pm 3 \Omega$

(2) Auto opsezi:

	Opseg	Rezolucija	Preciznost
10A	400 $\mu\Omega$ ~ 60.000 m Ω	1 $\mu\Omega$	$\pm 0.25\% \pm 25 \mu\Omega$
1 A	4.00 m Ω ~ 600.00 m Ω	10 $\mu\Omega$	$\pm 0.25\% \pm 250 \mu\Omega$
100 mA	0.0400 Ω ~ 6.0000 Ω	100 $\mu\Omega$	$\pm 0.25\% \pm 2.5 \text{ m}\Omega$
10 mA	0.400 Ω ~ 60.000 Ω	1 m Ω	$\pm 0.25\% \pm 25 \text{ m}\Omega$
1 mA	4.00 Ω ~ 600.00 Ω	10 m Ω	$\pm 0.25\% \pm 250 \text{ m}\Omega$
100 μA	0.0400 k Ω ~ 6.0000 k Ω	100 m Ω	$\pm 0.75\% \pm 3 \Omega$

Generalne specifikacije:

Izvor napajanja:	Dopunjiva litijumska baterija, 3400mAh (11.1V)
Vreme dopunjavanja baterije:	10 sati
Punjenje baterije:	AC 110V ili 220V ulaz, DC 15V / 1~3A izlaz Molimo primetite polaritet DC
LCD displej:	4 5/6 cifara LCD + Pozadinsko osvetljenje
Dimenzije:	257(L) x 155(W) x 57(H) mm
Težina:	1160g (sa baterijom)
Radna sredina:	-10°C ~ 50°C 85% RH
Skladišna sredina:	-20°C ~ 60°C 75% RH
Standardni dodaci:	RS232C (na USB Bridge) kabl x 1 Dopunjiva litijumska baterija x 1 AC adapter x 1 Kelvin štipaljke x 1 set Uputstvo za upotrebu x 1 Softver CD x 1 Uputstvo za upotrebu softvera x 1
Opcije:	4-žični Test kablovi



Melco Buda d.o.o.

- kancelarija u Beogradu: Hadži Nikole Živkovića br.2
Poslovna zgrada Iskra komerc, kancelarija 15/ II sprat
tel: 011/ 2181 609, tel/faks: 011/ 3286 445

e mail: office-beograd@melcobuda.co.rs , budimir.melcobuda@gmail.com
www.melcobuda.co.rs , www.kyoritsu-instrumenti.com , www.termovizija.com

- kancelarija u Despotovcu: Saveza Boraca br.7, 35213 Despotovac, Srbija
tel:035/612 916, faks:035/613 319, mob. 063/8003370
e mail: office@kyoritsu-instrumenti.com , office@melcobuda.co.rs

- Germany address: Quer strasse 18 Offenbach